



高鐵儀器 精密卓越



GOTECH "the best partner" to raise your competition

GT-7017-EM1/EL1 老化試驗機 Aging Oven

GB/T 3903.35-2008、ISO 18895:2006

本機用於測試塑膠類、橡膠類、皮革類、布類材料受熱前與受熱後之變化特性。經規定溫度及時間均勻受熱後，觀測試樣老化前後之耐黃、開膠、收縮、伸長、殘餘率等性能，從而判定其老化特性。

This machine is used for testing changes in characteristics of plastics, rubber, leather and fabrics before and after heating. The specimen is checked to see its discoloration, split, shrinkage, extension, residual ratio, etc. so as to determine the aging characteristics.

型號 Model	GT-7017-EM1	GT-7017-EL1
溫度範圍 Temp. range	常溫 Room temp. +10°C ~ 300°C	
溫度控制方式 Temp. control	採LCD面板按鍵式控制方式，可做多點精度校正	
溫度偏差 Temp. deviation	100°C以內 within < ±1°C	
	100 ~ 200°C以內 within < ±2°C	
	200 ~ 300°C以內 within < ±3°C	
溫度波動度 Temp. fluctuation	±0.5°C	
溫度均勻度 Temp. uniformity	±1% F.S	
定時器 Timer	0 ~ 9999 (H、M)可設定 Switchable	
回轉盤速度 Turntable speed	5 ~ 10 rpm	
視窗 Viewing window	可視鋼化玻璃，箱內照明25W	
	Tempered glass, and 25W lamp	
加熱絲功率 Heater power	3.5kw	
內箱 Interior(W×D×H)	40×40×45 cm	50×50×60 cm
體積 Dimension(W×D×H)	70×88×143 cm	95×78×156 cm
重量(約) Weight	179 kg	
電源 Power	1φ, AC 220V, 50Hz, 4kW(依國別或指定 Specified by user)	



瞭解更多產品資訊，請登錄我司網站 www.gotech.biz



創於1977年

高鐵科技股份有限公司

GOTECH TESTING MACHINES INC.

本廠: 台中市工業區24路28號

二廠: 台中市工業區24路31號

TEL: (04)23590061 FAX: (04)23591553

網址: www.gotech.biz E-mail: gt112@gotech.biz

高鐵檢測儀器(東莞)有限公司

GOTECH TESTING MACHINES CO., LTD.

地址: 廣東省東莞市南城區宏圖高科技開發區宏三路

TEL: 0769-89986666 22400899 FAX: 0769-22400699

E-mail: gt-d130@gotech.biz 手機: 13926831580

高特威爾檢測儀器(青島)有限公司

GOODTECHWILL TESTING MACHINES CO., LTD.

地址: 中國青島市市北區哈爾濱路52號青建太陽島1號商務樓8層

TEL: 0532-85931956 85931957 FAX: 0532-85931950

E-mail: gt-q101@gotech.biz 手機: 13708970121